



**Wiremold**  
**Cord Ended deQuorum™ Single-Flip Up Unit**  
Part No. DQFP15ST



Unit includes one (1) 15A black tamper-resistant duplex receptacle. Unit comes with a 6' (1.83m) cord. Comes with a brushed stainless steel finish.

## Features & Benefits

**Sleek, Attractive Design:** Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

**Tamper-Resistant Receptacles:** Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

**New Soft Opening Cover Mechanism:** Opening and closing the cover is quieter and easier with a more professional feel.

**Expanded Configuration Options:** Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

**UL Spill Water Protection:** Meets and exceeds UL1363 standard for relocatable power taps. Eliminates risk of shock or short circuiting due to moisture entering device.

**USB Charging Capability:** Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

**Multiple Cover Finish Options:** Durable black powder coat and brushed stainless steel finishes blend with most decors.

**cULus Listed:** Meets UL US and Canadian safety standards for Relocatable Power Taps (File E66421, Guide XBY5) and Multitoutlet Assemblies (File E15191, Guide PVGT).

## Specifications

### General Info

|              |              |                       |                  |
|--------------|--------------|-----------------------|------------------|
| Product Line | Wiremold     | Color                 | Stainless Steel  |
| UPC Number   | 786776184525 | Country Of Origin     | Mexico           |
| Material     | Aluminum     | Number of Receptacles | 1                |
| Construction | Die Cast     | Outlet Type           | Tamper-Resistant |

|                                       |                                                                                       |                   |                                                                                                                                                          |
|---------------------------------------|---------------------------------------------------------------------------------------|-------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application Sector                    | Commercial, Education, Entertainment, Healthcare, Hospitality, Parks, Retail, Transit | Standard          | cULus Listed<br>Relocatable Power Tap: File E66421<br>Guide XYBS, cULus Listed Multioutlet Assembly: File E15191<br>Guide PVGT, Meets Article 380 of NEC |
| Warranty Type                         | 1-Year from Installation or 2-Years from Day of Sale                                  | Type              | Flip Up                                                                                                                                                  |
| Dimensions                            |                                                                                       |                   |                                                                                                                                                          |
| Product Width US                      | 4.75 in                                                                               | Product Weight US | 3.9 lb                                                                                                                                                   |
| Product Length US                     | 5.625 in                                                                              | Internal Depth    | 3.25 in                                                                                                                                                  |
| Listing Agencies / 3rd Party Agencies |                                                                                       |                   |                                                                                                                                                          |
| cULus Listed                          | Yes                                                                                   |                   |                                                                                                                                                          |
| Trade Programs                        |                                                                                       |                   |                                                                                                                                                          |
| USMCA                                 | Yes                                                                                   |                   |                                                                                                                                                          |
| Additional Information                |                                                                                       |                   |                                                                                                                                                          |
| RoHS Compliant                        | Yes                                                                                   |                   |                                                                                                                                                          |
| Technical Information                 |                                                                                       |                   |                                                                                                                                                          |
| Cord Length                           | 6 ft                                                                                  | Amperage          | 15 A                                                                                                                                                     |
| Cable Entry                           | Below                                                                                 | Wiring Method     | Cord-ended                                                                                                                                               |
| NEMA Configuration Code               | 5-15R                                                                                 | Mounting Type     | Recessed                                                                                                                                                 |
| Cutout Shape                          | Rectangular                                                                           | Voltage           | 125.0 V                                                                                                                                                  |