



Wiremold
Evolution™ Series 8-Gang Hinged Wall Box
Part No. EHWP8-WH



Designed to fit into the 16" on center (406mm) opening between studs in a standard 2"x 4" (51mm x 102mm) wall. For both new work and old work applications. The box has two (2) 4-gang standard NEMA size openings and designed to accommodate power, communications, and A/V devices. Each box includes tunnel that allows wiring compartments on both sides of the box to be fed with a single conduit, reducing time and construction cost. The box has been designed with a cable pass through capability allowing multiple service points to be daisy chained together, eliminating the need for multiple conduit runs. Box includes temporary cover. Finished cover assembly (EHWBC) sold separately.

Features & Benefits

Available in both 4- and 8-gang versions to provide maximum flexibility.	Built-in tunnel & feed through capability allows service feeds to be fed through the box, reducing the number of feeds required to reduce installation time.
Cover opens a full 180° and can be painted to blend with room decor. Includes integrated handle, lock and key set for security, and flush egress door for cabling.	Designed to accept standard 1- to 4-gang device plates. No proprietary plates simplifies ordering and installation.
Accepts Legrand AVIP devices, plus A/V devices from leading manufacturers.	3 5/8" [92mm] of space behind device plates provides the extra depth needed for wiring larger A/V devices.
Accepts trade size service feeds from 3/4" up to 2". Knockout plates are removable and interchangeable, providing multiple options.	Can be installed in new work and old work installations. New hardware not necessary.
Both boxes (4- and 8-gang) fit are designed to fit in 16" opening between studs in standard 2" x 4" [51mm x 102mm] wall.	UL Listed to U.S. and Canadian safety standards.
Finished interior eliminates industrial look for upscale installations, while increasing visibility, making it easier to locate.	

Specifications

General Info

Product Line	Wiremold	Color	White
UPC Number	786564085676	Country Of Origin	United States
Material	Steel	Construction	Assembled

Features	Tunnels	Application Sector	Commercial, Education, Healthcare, Hospitality
Standard	cULus Listed Metallic Outlet Boxes: File E2961 Guide QCIT Meets Article 314.27(C) of NEC.	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Wall Box		
Dimensions			
Product Width US	10.5 in	Product Weight US	13.95 lb
Product Depth US	3.97 in	Product Length US	10.5 in
Cubic Capacity	113.8 in ³	Knockout Size	1-1/4 in, 2 in, 3/4 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Service Capacity	Dual	Number of Gangs	8
Cable Entry	Knockout	Depth Behind Device Plates	3.63 in