



Wiremold
RC3 Multi-Service Poke-Thru Assembly, Gray
Part No. RC3ATCGY



Assembled unit. Prewired 20A duplex receptacle can be wired as a standard duplex receptacle or isolated ground. Flange available in painted gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS). Slide covers match the painted flange colors: gray, black, and ivory. Aluminum and brass flanges shipped with black slide cover. Brass flange also available with nonmetallic brass colored slide holder (AB). Aluminum flange also available with nonmetallic aluminum colored slide holder (AA). Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers. Unit also includes two Ortronics TracJack adapters and two Ortronics Series II adapters. Modular jacks sold separately. NOTE: Assembled with scrub water gasket. For use on tile or carpet floors. RC3 Series Poke-Thru Devices require a 4inch (102mm) diameter hole. Not designed to work with bare concrete or terrazzo. Floor covering thickness 1/8inch minimum.

Features & Benefits

Assembled unit Prewired 20A duplex receptacle can be wired as a standard duplex receptacle or isolated ground	Flange available in painted gray (GY), black (BK), ivory (VY) or brushed metal finishes in aluminum (AL), and brass (BS)
Slide covers match the painted flange colors: gray, black, and ivory	Aluminum and brass flanges shipped with black slide cover
Brass flange also available with nonmetallic brass colored slide holder (AB)	Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers
Includes Wiremold Open System unloaded adapters to accept four discrete keystone connectors from most manufacturers	Unit also includes two Ortronics TracJack adapters and two Ortronics Series II adapters
Modular jacks sold separately	NOTE: Assembled with scrub water gasket
For use on tile or carpet floors	Modular jacks sold separately
Not designed to work with bare concrete or terrazzo	Floor covering thickness 1/8" minimum

Specifications

General Info

Product Line	Wiremold	Color	Gray
UPC Number	786564067009	Country Of Origin	Mexico
Material	Steel	Number of Knockouts	2
Application Sector	Commercial, Education, Healthcare, Hospitality	Standard	UL Fire Classified, cULus, NEC

Warranty Type	1-Year from Installation or 2-Years from Day of Sale	Type	Poke-Thru
Dimensions			
Product Width US	7.5 in	Product Weight US	5.247 lb
Product Volume US	900.0 cu in	Product Depth US	16.0 in
Product Height US	7.5 in	Cubic Capacity	24.5 in³
Core Hole Size	4 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E2961	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes	Product Environmental Profile	Yes
Technical Information			
Floor Type	Carpet, Tile	Is Pre-Wired	Yes
Service Capacity	Dual	Fire Rating	2 hr
Number of Outlets	2		