



Wiremold  
**InteGreat™ A/V TABLE BOX WITH USB, FIELD WIRED, ALUMINUM**  
Part No. TB672AUALF



InteGreat™ A/V table boxes are an elegant solution for extending power, communication and A/V to the meeting presenter's point-of-use. InteGreat™ A/V table boxes provide the depth to mount devices, especially A/V devices, below the table top. It has attractive finishes that can match any room decor. Combine it with other InteGreat™ products for a comprehensive solution to managing and delivering power, communication and A/V connectivity for conference rooms. This field wired version can be easily installed using MC type cable. The wiring compartment contains leads with easy to wire Wago® splicing connectors. Now available with two USB A charging ports.

## Features & Benefits

InteGreat™ A/V Table Boxes have a brushed, anodized cover available in either black or aluminum finishes, with beveled edges and a "soft-touch" handle

A finishing plate hides hardware on the activation surface and allows for labeling of the AVIP plates

Ease of Installation. Hole cuts are made easy with the included template. Simply configure your connectivity, set your activation height, place box in the cut out, and secure it below the table with the bracket and set screw.

USB Charging - InteGreat™ A/V Tables Boxes come standard with 2 USB-A Charging Ports, 3.1A shared.

Each box also has two 15 amp receptacles in the top compartment and one 15 amp receptacle on the underside of the box.

The "pocket" door in the cover fully recesses into the box when open, giving access to connections without obstructing the work surface

The activation surface of the InteGreat™ A/V Table Box can be adjusted down, in 1/2" [12.7mm] increments, from 1" to 4" [25mm to 102mm] to allow the cover to close even when using large style connectors.

InteGreat™ A/V Table Boxes are supplied with a cable grommet kit that can accommodate up to eight pull out connections. Boxes can also accept up to five Wiremold AVIP, or Extron® MAAP connectors.

The cover flange allows for 1/4" [6.4mm] of forgiveness in the cut out opening. InteGreat™ A/V Table Boxes have a 12' SJT cord for easy connection to the electrical infrastructure.

## Specifications

### General Info

|              |              |                       |               |
|--------------|--------------|-----------------------|---------------|
| Product Line | Wiremold     | Color                 | Aluminum      |
| UPC Number   | 786776192353 | Country Of Origin     | United States |
| Material     | Aluminum     | Number of Receptacles | 2             |

|                                       |                                                      |                         |             |
|---------------------------------------|------------------------------------------------------|-------------------------|-------------|
| Features                              | USB-A Charging                                       | Application Sector      | Commercial  |
| Warranty Type                         | 1-Year from Installation or 2-Years from Day of Sale | Type                    | Table Box   |
| Dimensions                            |                                                      |                         |             |
| Product Width US                      | 6.0 in                                               | Product Weight US       | 7.71 lb     |
| Product Depth US                      | 8.25 in                                              | Product Length US       | 6.937 in    |
| Internal Depth                        | 8.25 in                                              |                         |             |
| Listing Agencies / 3rd Party Agencies |                                                      |                         |             |
| ETL Listed                            | Yes                                                  | CSA Listed              | Yes         |
| CSA File Number                       | 101415836CRT-002                                     |                         |             |
| Trade Programs                        |                                                      |                         |             |
| USMCA                                 | Yes                                                  |                         |             |
| Additional Information                |                                                      |                         |             |
| RoHS Compliant                        | Yes                                                  |                         |             |
| Technical Information                 |                                                      |                         |             |
| USB Wattage                           | 15 W                                                 | USB Amperage            | 3.1 A       |
| Number of USBs                        | 2                                                    | Amperage                | 15 A        |
| Wiring Method                         | Cord-ended                                           | NEMA Configuration Code | 5-15R       |
| Mounting Type                         | Recessed                                             | Cutout Shape            | Rectangular |
| Voltage                               | 125.0 V                                              |                         |             |