



Wiremold  
2000 Entrance End Fitting Fitting  
Part No. V2010A3



1/2" trade size KOs located on end, sides, and bottom of fitting.  
3/4" KOs on bottom and rear. Includes ground screw.

## Features & Benefits

1/2" trade size KOs located on end, sides, and bottom of fitting. 3/4" KOs on bottom and rear. Includes ground screw.

## Specifications

### General Info

|              |              |                   |               |
|--------------|--------------|-------------------|---------------|
| Product Line | Wiremold     | Color             | Ivory         |
| UPC Number   | 786776009606 | Country Of Origin | United States |
| Material     | Steel        | Product Series    | 2000 Series   |

|                                       |                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |           |
|---------------------------------------|--------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------|
|                                       |                                                                          | cULus Listed<br>Base & Blank<br>Cover: File E4376<br>Guide RJBT.<br>Multioutlet<br>Assemblies: File<br>E15191 Guide<br>PVG. Fittings:<br>File E41751<br>Guide RJPR.<br>Base & Blank<br>Cover &<br>Plugmold Series<br>w/Snapicoil<br>Haarness: Meets<br>Article 386 of<br>NEC. Meets<br>Section 12-3032<br>of CEC. cULus<br>Listed Raceway:<br>File E4376 Guide<br>RJBT. Fittings:<br>File E41751<br>Guide RJPR.<br>Base & Black<br>Cover: Meets<br>Article 386 of<br>NEC. Meets<br>Section 12-600 of<br>CEC. |           |
| Application Sector                    | Commercial, Education, Entertainment,<br>Healthcare, Hospitality, Retail | Standard                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |           |
| Warranty Type                         | 1-Year from Installation or 2-Years from<br>Day of Sale                  | Type                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         | Fitting   |
| Dimensions                            |                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |           |
| Product Width US                      | 1.3 in                                                                   | Product Weight US                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | 0.73 lb   |
| Product Depth US                      | 3.0 in                                                                   | Product Height US                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | 2.6875 in |
| Product Length US                     | 3.0 in                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |           |
| Listing Agencies / 3rd Party Agencies |                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |           |
| cULus ListingNumber                   | E41751                                                                   | cULus Listed                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 | Yes       |
| Trade Programs                        |                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |           |
| USMCA                                 | Yes                                                                      |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |           |

---

Additional Information

---

|                |     |                               |     |
|----------------|-----|-------------------------------|-----|
| RoHS Compliant | Yes | Product Environmental Profile | Yes |
|----------------|-----|-------------------------------|-----|

---

Technical Information

---

|                |        |               |            |
|----------------|--------|---------------|------------|
| Indoor/Outdoor | Indoor | Mounting Type | On Surface |
|----------------|--------|---------------|------------|

---

|         |         |                          |                        |
|---------|---------|--------------------------|------------------------|
| Voltage | 300.0 V | Environmental Conditions | Dry interior locations |
|---------|---------|--------------------------|------------------------|

---