



MatixGo

- One-way axial switches
- Two-way axial switches
- Four-way axial switches
- Axial pushbutton


JW4051 - JG4051 - JB4051
JW4053 - JG4053 - JB4053
JW4054 - JG4054 - JB4054
JW4054LB - JG4054LB - JB4054LB
W4054V127LB - JG4054V127LB - JB4054V127LB
JW4055 - JG4055 - JB4055



..4051
 ..4053
 ..4055



..4054



..4054LB
 ..4054V127LB

Use

Rocker control device for lighting and other loads.


Range

Designation	Item
One-way axial 1P 10AX - 250Va.c. lighttable with led lamp (see table below) 1 module	☐ JW4051 ☐ JG4051 ☐ JB4051
Two-way axial 1P 10AX - 250Va.c. lighttable with led lamp (see table below) 1 module	☐ JW4053 ☐ JG4053 ☐ JB4053
Four-way axial 1P 10AX - 250Va.c. not lighttable 1 module	☐ JW4054 ☐ JG4054 ☐ JB4054
Four-way axial 1P 10AX - 250Va.c. Supplied with blue LED for backlighting (the LED is not interchangeable) - 1 module	☐ JW4054LB ☐ JG4054LB ☐ JB4054LB
Four-way axial 1P 10AX - 127Va.c. Supplied with blue LED for backlighting (the LED is not interchangeable) - 1 module	☐ JW4054V127LB ☐ JG4054V127LB ☐ JB4054V127LB
Axial pushbuttons 1P NO 10A - 250Va.c. lighttable with led lamp (see table below) 1 module	☐ JW4055 ☐ JG4055 ☐ JB4055

LED Color	230 Va.c.	12/24 Va.c.	127 Va.c.
White	LN4743/230T	LN4743/12T	LN4743/127T
Blue	H4743/230B	H4743/12B	H4743/127B

Colors: ☐ White ☐ Grey ☐ Black

Overall dimensions (mm)



	A	B	C	D
..4051 / ..4053 / ..4055	45.1	22.3	33.8	7.6
..4054	45.1	22.3	38.2	7.6

Connection

Terminal type: screw clamp
 Terminal capacity: 2 x 4 mm² max
 Stripping length: 9 mm
 Compatible with flexible or rigid cables

Technical characteristics

- **Protection index:**
(considering a complete installation, including cover plate)
 - Penetration by solid bodies/liquid: IP40
 - Impact test: IK04
- **Material characteristics:**
 - Case: PC (polycarbonate)
 - Key cover: ABS
 - Halogen Free
 - UV resistant
 - Self-extinguishing:
- 850°C/30s for insulating parts holding live parts in place.
650°C/30s for other parts made of insulating material.
- **Electrical characteristics:**
 - Voltage: 250 V a.c.
 - Current: 10AX for ..4051 - ..4053 - ..4054..
 - Current: 10A for ..4055
- **Climatic characteristics:**
 - Storage temperature: -10° C a +70° C
 - Use temperature: -5° C a +35° C

Cleaning

Clean the surface with a cloth.
 Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN 60669-1.

Refer to e.catalogue.