


MatixGo

JW4351V12 - JG4351V12 - JB4351V12
JW4351V230 - JG4351V230 - JB4351V230
JW4356V12 - JG4356V12 - JB4356V12
JW4356V230 - JG4356V230 - JB4356V230

Acoustic signal devices



Use


Acoustic signal devices: buzzer, bronze bell.

Range

Designation	Item
Bronze bell 5VA - 12 Va.c. - 80dB - 1 module	☐ JW4351V12
	☐ JG4351V12
	☐ JB4351V12
Bronze bell 8VA - 230Va.c. - 80dB - 1 module	☐ JW4351V230
	☐ JG4351V230
	☐ JB4351V230
Buzzer 5VA - 12 Va.c. - 80dB - 1 module	☐ JW4356V12
	☐ JG4356V12
	☐ JB4356V12
Buzzer 8VA - 230Va.c. - 80dB - 1 module	☐ JW4356V230
	☐ JG4356V230
	☐ JB4356V230

Colors: ☐ White ☐ Grey ☐ Black

Overall dimensions (mm)



A	B	C	D
45.1	22.5	42.7	7.6

Connection

Terminal type: screw clamp
Terminal capacity: 2 x 2.5mm² max
Stripping length: 9 mm
Compatible with flexible or rigid cables

Technical characteristics

- **Protection index:**
(considering a complete installation, including cover plate)
 - Penetration by solid bodies/liquid: IP40
 - Impact test: IK04
- **Material characteristics:**
 - Case: PC (polycarbonate)
 - Cover: ABS
 - Halogen Free
 - UV resistant
 - Self-extinguishing:
850°C/30s for insulating parts holding live parts in place.
650°C/30s for other parts made of insulating material.
- **Electrical characteristics:**
 - J.4351V230 - J.4356V230
 - Voltage: 230 V a.c.
 - Current: 8VA
 - J.4351V12 - J.4356V12
 - Voltage: 12 V a.c.
 - Current: 5VA
- **Climatic characteristics:**
 - Storage temperature: -10° C a +70° C
 - Use temperature: -5° C a +35° C

Cleaning

Clean the surface with a cloth.
Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN/62080.

Refer to e.catalogue.