




adorne Collection
adorne® 15A 2-Gang Pop-Out Triplex Outlet Kit, White
Part No. ARPTR1522GW2



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 3-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety.

Provides additional power with 3-plug access when extended from wall.

Disappears back into the wall with a simple push when not needed.

Installs easily in as little as 15 minutes.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007432473
Country Of Origin	China	Number of Receptacles	3
Features	Pop-Out	Outlet Type	Pop-Out, Tamper-Resistant
Application Sector	Multi-Dwelling Unit, Residential	Wall Plate Included	No
Warranty Type	Limited Lifetime Warranty		

Dimensions

Product Width US	4.8 in	Product Depth US	2.6 in
Product Height US	4.7 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Energy Savings	No		
Technical Information			
Connection Location	Back Only	Terminal Accommodation	#14 AWG - #12 AWG
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Number of Phases	1	Wire Connection Type	Internal Pressure Plates
Voltage	125.0 V		