



Step marker light and step marker light with IR



J..4382



J..4382IR

Use


Step marker light and step marker light with integrated IR.

Range

Designation	Item
Step marker light	☐ JW4382
	☐ JG4382
	☐ JB4382
Step marker light + IR	☐ JW4382IR
	☐ JG4382IR
	☐ JB4382IR

Colours code: ☐ White ☐ Grey ☐ Black

Overall dimensions (mm)



	A	B	C	D
J..4382	45.1	45.1	42.9	13
J..4382IR	45.1	45.1	46.1	16.2

Connection

Terminal type: screw clamp
Terminal capacity: 2 x 4 mm² max
Stripping length: 8 mm
Screwdriver: flat 3
Compatible with flexible or rigid cables

Technical characteristics

- Protection index

(considering a complete installation, including cover plate)
Penetration by solid bodies/liquid: IP40

- Mechanical characteristics

Impact test: IK 04

- Material characteristics

Material:
Case and Key cover: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing:

850° C / 30 s for insulating parts holding live parts in place
650° C / 30 s for other parts made of insulating materials

- Electrical characteristics

Voltage:
J..4382 - 230V a.c.
J..4382IR - 230V a.c.
Power consumption : 1W

- Climatic characteristics

Storage temperature: - 10° C to + 70° C
Use temperature: - 5° C to + 35° C

Cleaning

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards EN-60669-1
Refer to e.catalogue.