


MatixGo

Charger USB - 63W - Type C+C Power Delivery

JW4395CC - JG4395CC - JB4395CC



Type-C+C

Use

USB to charge portable devices such as phones, smartphone, MP3 o MP4 tablet, speakers, watches, game consoles, powerbanks. Ottimizza la velocità di ricarica dei terminali Power Delivery.

USB Power Delivery is a new fast charging technology integrated into iOS/Apple e Android/Google device.


Technology that allows a faster charger level than conventional technology, operating through an exchange between the terminal and the charger.

Range

Description	Item
USB charger with two type C ports for charging electronic device up to 20W. It allows the fast charging of portable device (tablets, Smartphones) equipped with power delivery technology.	☐ JW4395CC
Output voltage : 5 - 9 - 12 - 15 - 20 Vdc	☒ JG4395CC
DIRECT Power supply 220-240 V - 50-60 Hz	☒ JB4395CC
3 modules	

Colore: ☐ Bianco ☒ Grigio ☒ Nero

Dimensions (mm)



Connection

Type of terminals: automatic

Capacità del morsetto: 2 x 2.5 mm²

Stripping length: 6 mm

Compatibile with flexible and rigid wire

Circuit breaker: MAX. 16A

Imperative safety precautions:



Switch OFF the power at the main circuit breakers. Make sure the power is OFF before continuing with installation.

Technical characteristics

Protection index:

(Assembly complete cover-plate - supporting frame)

- Penetration by solid bodies and liquid : IP40
- Impact test: IK 04

Material characteristics:

- Case: PC classe V-0
- Cover : PC classe V-0
- Halogen Free
- UV-resistant
- Self-extinguishing :

850°C/30s For insulating part that keep in position parts in tension

650°C/30s For other parts of insulating materials

Electrical characteristics :

All values listed below are measured at an ambient temperature of + 20° and after 30 minutes of operation.

Nominal input voltage	220-240 V~
Nominal input frequency	50/60 Hz
Nominal input current	0.8 A
Max nominal output current	3.0 A(*)
Max output power	63 W
Nominal output voltage	5.0 V~ *
Average efficiency in active mode	81%
Stand-by power consumption	< 0.3 W

Consumption class without load and average level of efficiency : livello VI

Protection class	II - Low voltage
------------------	------------------

* Optimized voltage: 1 output

5.0 V~	3.0 A
9.0 V~	3.0 A
12.0 V~	3.0 A
15.0 V~	3.0 A
20.0 V~	3.0 A

* Optimized voltage: 2 outputs

Tablet		Phone	
5.0 V~	3.0 A	5.0 V~	3.0 A
9.0 V~	3.0 A	9.0 V~	2.0 A
12.0 V~	3.0 A	12.0 V~	1.5 A
15.0 V~	3.0 A		
20.0 V~	2.2 A		

Climate characteristics :

- Storage temperature: from -20° C to +70° C
- Operating temperature: from -5° C to +40° C

Cleaning

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution:

Always test before using other special cleaning product

Standards and approvals

Compliant with installation and manufacturing standards.

See e.catalogue.