



adorne Collection
adorne® 700W Incandescent/Halogen Motion Sensor Dimmer, White, with Microban®
Part No. ADSM703HW2



Perfect for garages and pantries, this dimmer switch allows for both manual and automatic motion-activated control. Using motion-sensing technology, it automatically turns lights on when you enter a room, and off when you leave. With manual control, you can even adjust to your preferred light level with the subtle built-in slider. Use on its own to control an incandescent or halogen light or fixture from a single location, or pair with a second Motion Sensor Dimmer to use as a remote dimmer switch for control of a single light source from two locations. This Motion Sensor Dimmer is meant for single fixtures and small lighting groups that do not exceed 700W.

This dimmer* features enduring Microban Registered antimicrobial technology that works to reduce the growth of bacteria, around the clock, for the lifespan of the product.

* Existing inventory of switches, dimmers and plastic wall plates from the adorne Registered Collection at some partner locations may not yet include Microban Registered protection. To confirm that a specific Legrand product is protected with Microban Registered, check that the exterior of the product packaging includes a green dot or a "Protected with Microban" label. Made exclusively for use with screwless Wall Plates from the adorne Registered Collection, sold separately.

No antimicrobial efficacy claims are being made or are valid with respect to products sold in Canada.

Features & Benefits

Helps fight the growth of stain and odor-causing bacteria through the invisible and continuous product protection of Microban® antimicrobial technology

Installs in 15 minutes or less, fitting into an existing electrical box. No new wiring required for typical installation.

Usable in both single-pole and 3-way applications.

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

For use with dimmable incandescent/halogen bulbs or fixtures. Features manual control (for power and light level), as well as automatic control through motion-sensing technology.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Gloss	UPC Number	785007023428
Country Of Origin	China	Material	Polycarbonate
Features	Adjustable Time Delay, Antimicrobial Protection, Dimming, Light Level Sensor, Motion Sensor	Switch Type	Motion Sensor, sofTap
Number of Switches	1	Installation Location	Wall Box

Application Sector	Hospitality, Light Commercial, Multi-Dwelling Unit, Residential		Standard	cULus
Warranty Type	Limited Lifetime Warranty			
Dimensions				
Product Width US	1.85 in	Product Depth US	1.77 in	
Product Height US	4.2 in			
Technical Information				
Load Rating	120V 450W (CFL), 120V 450W (LED), 120V 700W (Halogen), 120V 700W (Incandescent)	Sensor Coverage Pattern	180 °	
Sensor Type	Occupancy, Vacancy	Sensor Technology	Passive Infrared (PIR)	
Timer Duration	15 Minutes, 30 Seconds-30 Minutes	Number of Poles	Single Pole 3 Way	
Wire Size	#14 - #10 AWG	Trim/Adjustment Level	Button	
Dimming Phase	Forward	Input Voltage	120 VAC	
Requires Neutral Wire	No	Line Frequency	60 Hz	
Indoor/Outdoor	Indoor	Sensor Coverage	600 sq ft	
Wattage	700 W	Mounting Type	Wall Box	
On Function	Selectable Auto/Manual	Operating Humidity	0-95% RH (Non-Condensing)	
Sensing Range	Major Motion 35 ft, Minor Motion 20 ft	Wire Connection Type	Screw Terminals	
Voltage	120 VAC	Connection Type	Internal Pressure Plates	
Load Type	CFL, Halogen, Incandescent, LED	Environmental Conditions	Residential Indoor Use Only	