



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of *Escherichia coli*, Gram (-) and *Staphylococcus aureus*, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

Features & Benefits

UL and CSA Listed

NSF (National Sanitation Foundation)
Certified

Patent Pending

Anti-microbial Additives Embedded in
polymer and inhibits Growth of Bacteria,
Molds, Mildews and Fungi

Anti-microbial Additive Resistant to Scuffing and Cleaning

Escherichia (E.Coli): - Log reduction greater
than 4.8, reduced surface bacteria by
greater than 99.99%

Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface
bacteria by greater than 99.97%

Salmonella : Log Reduction Greater Than
3.6, reduces surface bacteria by Greater
Than 99.97%

RoHS Compliant (Non-Halogenated)

Independently tested and Certified to JIS
Z2801 standards

Resistant to High Pressure Hose-down applications

Tongue & Groove Environmental Sealing

Keyed Body and Cover for Alignment

NEMA Type 4, 4x, 6, 6P and IP67 Protection

SteriGuard: Anti-microbial Wiring Devices are ideal for a wide range of applications
including food and beverage preparation, procession, & packaging: agriculture,
pharmaceutical, and health care.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007056983	Country Of Origin	United States
Features	Antimicrobial Protection	Application Sector	Commercial

Standard	CSA Listed, FSUL, UL Listed	Warranty Type	1-Year
Type	Connector		
Dimensions			
Product Height US	1.85 in	Product Length US	4.03 in
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes		
Technical Information			
Operating Temperature Min	-40 °C	Connector Style	Straight Blade
Flanged	No	Terminal Accommodation	#18 AWG - #12 AWG
Connection	Cable	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	15 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Operating Temperature	-40°-60°C	Number of Phases	1
Voltage	125.0 V	Environmental Conditions	Moisture Resistance NEMA 3R (Flip Lid Assemblies/Back Boxes) Flammability UL94V0 (boxes & wiring device interiors) UL94V2 (cover plates) UL94HB (wiring device housings, flip lid seals) Operating Temperature - 40°C (without impact) to +60°C continuous UV Resistance All exposed materials are UV stabilized