



Pass and Seymour

Portable 2-Foot In-Line 15A Self-Test GFCI with Straight Blade Plug and Connector, Automatic Reset

Part No. 1597PC2A



The perfect option for safely powering portable equipment, outdoors or in, when a GFCI-protected outlet is not accessible. Use this 2-Foot In-Line Portable GFCI (Automatic Reset) when plugging in drills, saws, leaf blowers, pressure washers, power painters, etc.

Ground-Fault Circuit Interrupters (GFCI) help prevent electrical shock caused by ground faults. GFCI protection is required by code in bathrooms, kitchens, garages, outdoor areas, and for any other outlets found within six feet of a sink or water source.

Features & Benefits

Protects against electrical shock caused by ground-fault occurrences.

Conducts an industry-leading automatic self-test every 3 seconds. If the portable GFCI device ever fails, the red indicator light flashes to signal it should be replaced.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

Open neutral relay automatically cuts power to device line conductor if the neutral wire preceding the portable GFCI becomes damaged.

Automatically energizes portable GFCI for use upon plug-in and after loss of primary power.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Finish	Matte	UPC Number	785007381610
Country Of Origin	China	Features	Automatic Reset, Portable GFCI
Outlet Type	GFCI, Self-Test	Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	2.0 in	Product Weight US	0.9 lb
------------------	--------	-------------------	--------

Product Depth US	1.75 in	Product Length US	27.75 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	943	cULus Listed	Yes
Additional Information			
RoHS Compliant	Yes		
Technical Information			
Operating Temperature Min	-35 °C	Seismic Tested	No
Is Tamper-Resistant	No	Connection Location	Top and Bottom
Number of Wires	3	Operating Temperature Max	66 °C
Amperage	15 A	Number of Poles	Double Pole
Is Weather Resistant	No	Indoor/Outdoor	Outdoor
NEMA Configuration Code	5-15P, 5-15R	Operating Temperature	-35°-66°C
Voltage	125.0 V		