



Pass and Seymour
Turnlok® SteriGuard™ Antimicrobial Plug 15A, 125V, Yellow
Part No. 24W47AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

Features & Benefits

UL and CSA Listed

NSF (National Sanitation Foundation)
Certified

Patent Pending

Anti-microbial Additives Embedded in
polymer and inhibits Growth of Bacteria,
Molds, Mildews and Fungi

Anti-microbial Additive Resistant to Scuffing and Cleaning

Escherichia (E.Coli): - Log reduction
greater than 4.8, reduces surface bacteria
by greater than 99.99%

Staphylococcus (Staph), MRSA: - Log Reduction greater than 4.3, reduces
surface bacteria by greater than 99.97%

Salmonella : Log Reduction Greater Than
3.6, reduces surface bacteria by Greater
Than 99.97%

RoHS Compliant (Non-Halogenated)

Independently tested and Certified to JIS
Z2801 standards

Resistant to High Pressure Hose-down applications

Tongue & Groove Environmental Sealing

Keyed Body and Cover for Alignment

NEMA Type 4, 4x, 6, 6P and IP67 Protection

SteriGuard: Anti-microbial Wiring Devices are ideal for a wide range of
applications including food and beverage preparation, procession, & packaging:
agriculture, pharmaceutical, and health care.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007057058	Country Of Origin	United States

Features	Antimicrobial Protection	Application Sector	Industrial
Standard	UL Listed, CSA Listed	Warranty Type	1-Year
Type	Plug		
Dimensions			
Product Width US	1.85 in	Product Depth US	2.62 in
Product Height US	1.85 in		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes		
Technical Information			
Operating Temperature Min	-40 °C	Connector Style	Locking
Flanged	No	Terminal Accommodation	#18 AWG - #12 AWG
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	15 A	IP Rating	IP67
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	L5-15P	Operating Temperature	-40°- 60°C
Number of Phases	1	Voltage	125.0 V
Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized		