



Pass and Seymour
20A 250V Heavy Duty Specification Grade Single Decorator Receptacles, Black
Part No. 26861BK

Heavy-Duty Decorator Spec Grade Single Receptacle Back and Side-Wire
20A 250V



Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body.
- Heavy-duty compact design for easier installation and long lasting performance.
- Impact-resistant nylon face.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire.
- Tri-drive terminal and mounting screws.
- For covering patents, see www.legrand.us/patents.
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
- Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
- One-piece, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Terminal compartments isolated from each other for positive conductor containment.
- All devices fit standard #26 opening wall plate.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007786446	Country Of Origin	Mexico

Number of Receptacles	2	Features	Decorator Style, Impact Resistant, Single Piece Plated Steel Mounting Strap
Outlet Type	Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.322 in	Product Depth US	1.188 in
Product Length US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cUL ListingNumber	E140596	cUL Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Connection Location	Back and Side
Phase	Three	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-20R
Mounting Type	Box	Operating Temperature	-40°-60°C
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	250.0 V