



Pass and Seymour
20A 125V Industrial Extra Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Red
Part No. 5362ARED



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V

Features & Benefits

One-piece brass mounting strap with integral ground.	.032 inch thick, brass, triple-wipe power contacts for lasting retention.
Two drive screws anchor strap to back body and face.	Exclusive patented feature, circuit label on face allows permanent circuit identification.
.036 inch thick, brass, triple-wipe power contacts for lasting retention.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Oversized #10 deep tri-drive head brass terminal and ground screws.	Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .
Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact	

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007528176	Country Of Origin	Mexico
Number of Receptacles	2	Features	Brass Mounting Strap
Outlet Type	Straight Blade	Application Sector	Commercial, Industrial

Wall Plate Included	No	Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Connection Location	Back and Side	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Operating Temperature	-40°-60°C	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2