



Pass and Seymour
15A 250V Heavy Duty Spec-Grade Single Receptacle, Back and Side Wire, White
Part No. 5651W



Heavy-Duty Spec Grade Single Receptacle Side Wire 15A 250V

Features & Benefits

Auto-ground clip assures positive ground.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

One-piece brass triple-wire power contacts for lasting retention.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece heat-treated triple-wipe brass power contacts.

Backed-out tr-drive steel terminal screws.
Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007565133
Country Of Origin	Mexico	Number of Receptacles	1
Features	Heavy Duty Steel Mounting Strap	Application Sector	Commercial
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42

Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.38 in	Product Depth US	1.08 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Connection Location	Back and Side	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-15R
Operating Temperature	-40°-60°C	Wire Connection Type	Screw Terminals
Voltage	250.0 V		