



Pass and Seymour
20A 250V Heavy Duty Spec-Grade Single Receptacle, Side Wire, Ivory
Part No. 5851I

Heavy-Duty Spec Grade Single Receptacle, Side Wire 20A 250V



Features & Benefits

Auto-ground clip assures positive ground.

One-piece brass, triple-wire power contacts for lasting retention.

Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.

Backed-out tri-drive steel terminal screws.
Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.

One-piece brass triple-wire power contacts for lasting retention.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007585117
Country Of Origin	Mexico	Number of Receptacles	1
Features	Single Piece Plated Steel Mounting Strap	Outlet Type	Straight Blade
Application Sector	Commercial	Wall Plate Included	No
Standard	UL 498	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.38 in	Product Depth US	1.08 in
------------------	---------	------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Connection Location	Side Only
---------------------------	--------	---------------------	-----------

Number of Wires	3	Operating Temperature Max	60 °C
-----------------	---	---------------------------	-------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

NEMA Configuration Code	6-20R	Operating Temperature	-40°-60°C
-------------------------	-------	-----------------------	-----------

Wire Connection Type	Screw Terminals	Voltage	250.0 V
----------------------	-----------------	---------	---------