



Pass and Seymour
20A 250V Heavy Duty Spec-Grade Single Receptacle, Back and Side Wire, Red
Part No. 5871RED



Heavy-Duty Spec Grade Single Receptacle Back and Side Wire 20A 250V

Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece heat-treated triple-wipe brass power contacts.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
- Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
UPC Number	785007587142	Country Of Origin	Mexico
Number of Receptacles	1	Features	Single Piece Plated Steel Mounting Strap
Outlet Type	Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42, FDSPEC

Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.32 in	Product Depth US	1.093 in
Product Height US	1.68 in		
Listing Agencies / 3rd Party Agencies			
cUL ListingNumber	140596	cULus ListingNumber	E140596
cULus Listed	Yes	cUL Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection Location	Back and Side
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-20R
Wire Connection Type	Screw Terminals	Voltage	250.0 V
Environmental Conditions	Flammability: UL94 V2		