



Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 15A 250V

## Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

|                       |                                  |                     |                                          |
|-----------------------|----------------------------------|---------------------|------------------------------------------|
| Product Line          | Pass & Seymour                   | Color               | Ivory                                    |
| UPC Number            | 785007548914                     | Country Of Origin   | Mexico                                   |
| Number of Receptacles | 1                                | Features            | Single Piece Plated Steel Mounting Strap |
| Application Sector    | Commercial                       | Wall Plate Included | No                                       |
| Standard              | UL498, CSA C22.2 No. 42, FEDSPEC | Warranty Type       | 1-Year Limited Warranty                  |

### Dimensions

|                                       |                                           |                       |                          |
|---------------------------------------|-------------------------------------------|-----------------------|--------------------------|
| Product Width US                      | 1.32 in                                   | Product Depth US      | 1.093 in                 |
| Product Height US                     | 1.68 in                                   |                       |                          |
| Listing Agencies / 3rd Party Agencies |                                           |                       |                          |
| cUL ListingNumber                     | 140596                                    | cULus ListingNumber   | E140596                  |
| cULus Listed                          | Yes                                       | cUL Listed            | Yes                      |
| Technical Information                 |                                           |                       |                          |
| Operating Temperature Min             | -40 °C                                    | Dielectric Strength   | Withstands 2000V minimum |
| Connection Location                   | Back and Side                             | Number of Wires       | 3                        |
| Operating Temperature Max             | 60 °C                                     | Amperage              | 15 A                     |
| Number of Poles                       | Double Pole                               | Wire Size             | 14 - 10 AWG              |
| NEMA Configuration Code               | 6-15R                                     | Operating Temperature | -40°-60°C                |
| Wire Connection Type                  | Internal Pressure Plates, Screw Terminals | Voltage               | 250.0 V                  |
| Environmental Conditions              | Flammability: UL94 V2                     |                       |                          |