



Hard Use Spec Grade Combination Duplex Receptacle Side-Wire 20A 125/250V

## Features & Benefits

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body .032 inch thick, brass, triple-wipe power contacts to resist pulling away from face/body assembly. Impact-resistant nylon face.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Terminal compartments isolated from each other for positive conductor containment.

Tri-drive terminal and mounting screws.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

|                    |                |                   |                |
|--------------------|----------------|-------------------|----------------|
| Product Line       | Pass & Seymour | Color             | White          |
| UPC Number         | 785007042023   | Country Of Origin | United States  |
| Application Sector | Commercial     | Standard          | UL498, FEDSPEC |

### Dimensions

|                   |          |                  |         |
|-------------------|----------|------------------|---------|
| Product Width US  | 1.322 in | Product Depth US | 0.78 in |
| Product Height US | 2.635 in |                  |         |

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140596 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Technical Information

|                     |                          |                          |                       |
|---------------------|--------------------------|--------------------------|-----------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection               | Side Wire             |
| Number of Wires     | 3                        | Temperature Rating       | -40° - 60° C          |
| Amperage            | 20 A                     | Number of Poles          | Double Pole           |
| Wire Size           | 14 - 10 AWG              | Environmental Conditions | Flammability: UL94 V2 |