



Manual Control Switch 3-Pole 60A 600V in NEMA 3R Enclosure. Slotted opening on enclosures allows for lock-out, tag-out functionality.

Features & Benefits

High horsepower rating, up to 3HP for heavy-duty applications. Compact design provides ease of installation. Single piece moveable and stationary contact arms with oversized silver cadmium buttons provides excellent continuity and long life.

Type 3R enclosure has 2-1/2 inch, 3/4 inch, and 1 inch concentric knockouts on bottom. Accepts #4 AWG. cULus listed.

Made in USA. Box lug terminals. Wire pockets and thick wall arc barriers. Cold-rolled steel NEMA 3R enclosure with polyester urethane finish conforms to OSHA lockout requirements.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
Finish	Matte	UPC Number	785007078640
Country Of Origin	United States	Material	Aluminum
Features	Enclosed	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Manual Controller

Dimensions

Product Width US	1.74 in	Product Depth US	1.66 in
------------------	---------	------------------	---------

Product Height US	3.26 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	31169	cULus Listed	Yes
---------------------	-------	--------------	-----

Technical Information

Load Rating	60 A @ 600 VAC	Connection Location	Back and Side
-------------	----------------	---------------------	---------------

Horsepower Rating	3 HP @ 600 VAC	Terminal Accommodation	#14 AWG - #10 AWG
-------------------	----------------	------------------------	-------------------

Number of Gangs	1	Amperage	60 A
-----------------	---	----------	------

Number of Poles	3-Way	Requires Neutral Wire	Yes
-----------------	-------	-----------------------	-----

Indoor/Outdoor	Both	Mounting Type	On-Wall
----------------	------	---------------	---------

Wire Connection Type	Screw Terminals	Voltage	600.0 V
----------------------	-----------------	---------	---------

Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon
-----------	---