



Heavy-Duty Hospital Grade Single Receptacle, Back and Side-Wire, 15A 125V



Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007820355	Country Of Origin	Mexico
Number of Receptacles	1	Features	Single Piece Plated Steel Mounting Strap
Outlet Type	Hospital Grade	Application Sector	Commercial, Healthcare

Wall Plate Included	No	Standard	UL498, cUL/CSA C22.2 No. 42, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.32 in	Product Depth US	1.093 in
Product Height US	3.68 in		
Listing Agencies / 3rd Party Agencies			
cUL ListingNumber	E140596	cUL Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection Location	Back and Side
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Internal Pressure Plates	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2		