



Extra Heavy-Duty Hospital Grade Duplex Receptacle Back and Side-Wire 20A 250V

Features & Benefits

One-piece nickel-plated brass mounting strap with integral ground.	Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
Two drive screws anchor strap to back body and face.	Exclusive patented feature, circuit label on face allows permanent circuit identification.
.040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
Impact-resistant nylon face and back body.	Oversized #10 deep tri-drive head brass terminal and ground screws.
Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.	External nickel-plated screw-presure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
Line terminals accept #14 - #10 AWG stranded or solid copper-clad conductors.	Auto-ground clip assures positive ground.
Illuminated version features exclusive LED lamp with solder connection for long durable life (10-12 years).	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007156126	Country Of Origin	Mexico

Number of Receptacles	2	Features	Brass Mounting Strap
Outlet Type	Hospital Grade	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Connection Location	Back and Side	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	6-20R
Operating Temperature	-40°-60°C	Wire Connection Type	Screw Terminals
Voltage	250.0 V	Environmental Conditions	Flammability: UL94 V2 and UL94-5 VA