



radiant Collection

radiant® Dead-Front Dual Function 20A Duplex Self-Test AFCI/GFCI receptacle, Light Almond

Part No. AFGF202DFLA



Designed for applications where arc fault and ground fault protection is required but outlet access is not needed, the radiant® Dead-Front Dual Function Duplex Self-Test AFCI/GFCI receptacle is designed to protect against electrical fires and follow the National Electrical Code (NEC). This receptacle features an indicator light and accessible test and reset buttons that make trips easier to identify and resolve compared to AFCI breaker alternatives. Via a feed-thru wiring configuration, all outlets installed downstream are also protected. As a part of the radiant® Collection, it also features sleek, clean lines for a sophisticated look. Made for use with screwless Wall Plates from the Collection, sold separately.

Features & Benefits

Protects against fire caused by arc-fault and ground fault occurrences. Unlike breaker alternatives, AFCI/GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Dead front device is ideal for locations where plug-in access is not necessary.

Test and rest buttons located on face of device at point of use, making it easier to fix trips directly on the device.

SafeLock® Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly

Auto-ground clip assures a positive ground to a metal box

Dead front rated as 1 1/2 HP motor control switch

Compliant with NEC AFCI & GFCI requirements

Easier installation than breakers; fits any wall box; no need to match brand of breaker box

Accepts #14–#10AWG solid & stranded wires, Copper-clad aluminum, and copper wire

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007158342	Country Of Origin	China
Number of Receptacles	0	Features	Dead Front
Outlet Type	AFCI, Dead Front, GFCI	Application Sector	Residential

Wall Plate Included	Yes	Warranty Type	1-Year Limited Warranty
Dimensions			
Product Width US	1.74 in	Product Depth US	1.367 in
Product Height US	4.19 in	Product Length US	4.19 in
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
RoHS Compliant	Yes	Energy Savings	No
Technical Information			
Operating Temperature Min	-40 °C	Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG	Trip Range	5±1 mA
Number of Wires	3	Operating Temperature Max	60 °C
Number of Gangs	1	Amperage	20 A
Number of Poles	2 Pole	Indoor/Outdoor	Indoor
Mounting Type	Box	Operating Temperature	-40°-60°C
Wire Connection Type	Screw Terminal	Voltage	125.0 V