



Pass and Seymour
15A 125V Commercial Spec-Grade Duplex Receptacle, Side Wire, Ivory
Part No. CR15I

Commercial Spec Grade Duplex Receptacle, Side Wire 15A 125V



Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Auto-ground clip assures positive ground.
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
- Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007119060
Country Of Origin	Mexico	Number of Receptacles	2
Features	Impact Resistant, Single Piece Plated Steel Mounting Strap	Outlet Type	Straight Blade
Application Sector	Commercial	Wall Plate Included	No

Standard	UL 498	Warranty Type	1-Year Limited Warranty
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Operating Temperature Min	-40 °C	Connection Location	Side Only
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Mounting Type	Box
Operating Temperature	-40°-60°C	Wire Connection Type	Screw Terminals
Voltage	125.0 V		