



Pass and Seymour  
20A 125V Commercial Spec-Grade Duplex Receptacle, Side Wire, Red  
Part No. CR20RED

Commercial Spec Grade Duplex Receptacle, Side Wire 20A 125V



## Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Impact-resistant nylon face and thermoplastic back body.
- Terminal compartments isolated from each other for positive conductor containment.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
- Operating Temperature: Maximum continuous +50°C, minimum -40°C without impact

## Specifications

### General Info

|                    |                                                               |                       |                |
|--------------------|---------------------------------------------------------------|-----------------------|----------------|
| Product Line       | Pass & Seymour                                                | Color                 | Red            |
| Finish             | Matte                                                         | UPC Number            | 785007180145   |
| Country Of Origin  | Mexico                                                        | Number of Receptacles | 2              |
| Features           | Impact Resistant, Single Piece<br>Plated Steel Mounting Strap | Outlet Type           | Straight Blade |
| Application Sector | Commercial                                                    | Wall Plate Included   | No             |

|                                       |                         |                         |                          |
|---------------------------------------|-------------------------|-------------------------|--------------------------|
| Standard                              | UL498, CSA C22.2 No. 42 | Warranty Type           | 1-Year Limited Warranty  |
| Dimensions                            |                         |                         |                          |
| Product Width US                      | 1.322 in                | Product Depth US        | 0.78 in                  |
| Product Height US                     | 2.635 in                |                         |                          |
| Listing Agencies / 3rd Party Agencies |                         |                         |                          |
| cULus ListingNumber                   | E140596                 | cULus Listed            | Yes                      |
| Additional Information                |                         |                         |                          |
| Product Environmental Profile         | Yes                     |                         |                          |
| Technical Information                 |                         |                         |                          |
| Operating Temperature Min             | -40 °C                  | Dielectric Strength     | Withstands 1500V minimum |
| Connection Location                   | Side Only               | Number of Wires         | 3                        |
| Operating Temperature Max             | 60 °C                   | Amperage                | 20 A                     |
| Number of Poles                       | Double Pole             | Wire Size               | 14 - 10 AWG              |
| Indoor/Outdoor                        | Indoor                  | NEMA Configuration Code | 5-20R                    |
| Mounting Type                         | Box                     | Operating Temperature   | -40°-60°C                |
| Wire Connection Type                  | Screw Terminals         | Voltage                 | 125.0 V                  |