



Pass and Seymour

15A 125V Heavy Duty Spec-Grade Isolated Ground Decorator Duplex Receptacle, Back and Side Wire, Orange

Part No. IG26262



Isolated Ground Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Face color coding by voltage facilitates locating and mating of proper devices.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant plated steel strap.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
Finish	Matte	UPC Number	785007262629
Country Of Origin	Mexico	Number of Receptacles	2
Features	Decorator Style, Single Piece Plated Steel Mounting Strap	Outlet Type	Isolated Ground, Straight Blade
Application Sector	Commercial	Wall Plate Included	No
Standard	UL498, CSA C22.2 No. 42	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.322 in	Product Depth US	0.833 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection Location	Back and Side
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Wire Connection Type	Screw Terminals
Voltage	125.0 V		