



Pass and Seymour

15A 125V Heavy Duty Spec-Grade Isolated Ground Decorator Duplex Receptacle, Back and Side Wire, Black

Part No. IG26262BK



Isolated Ground Heavy-Duty Decorator Spec Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

Face color coding by voltage facilitates locating and mating of proper devices.

High-impact resistant nylon face resists impacts and scrapes.

Corrosion-resistant plated steel strap.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007268744	Country Of Origin	Mexico
Number of Receptacles	2	Features	Decorator Style, Single Piece Plated Steel Mounting Strap
Outlet Type	Isolated Ground, Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42, FEDSPEC
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.322 in	Product Depth US	0.833 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection Location	Back and Side
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Screw Terminals	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2		