



Construction 3-Way Switch, Back and Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 to #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007126273
Country Of Origin	Mexico	Material	Thermoplastic
Features	Single Piece Plated Steel Mounting Strap	Switch Type	Toggle
Number of Switches	1	Application Sector	Commercial, Industrial

Wall Plate Included	No	Standard	UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, FEDSPEC
Warranty Type	1-Year Limited Warranty	Type	Switch
Dimensions			
Product Width US	1.32 in	Product Depth US	1.073 in
Product Height US	3.281 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140597	cULus Listed	Yes
Technical Information			
Load Rating	20 A @ 120/277 VAC	Seismic Tested	No
Contact Configuration	One piece brass alloy contact arm	Connection Location	Back and Side
Horsepower Rating	1 HP @ 120 VAC, 2 HP @ 240 VAC	Terminal Accommodation	#14 AWG - #10 AWG
Contact Rating	Oversized silver alloy contacts	Number of Gangs	1
Throw Type	Double Throw	Amperage	20 A
Number of Poles	3-Way	Requires Neutral Wire	No
Indoor/Outdoor	Indoor	Mounting Type	Wall Box
Wire Connection Type	Screw Terminals	Voltage	120/277 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon	Degree of Protection	1500V Dielectric Withstand Voltage