



Pass and Seymour
20A, 125V Heavy Duty Spec Grade Plug Load Timer Receptacle
Part No. PLT26351I



New requirements for reducing energy consumption in commercial buildings are here. With devices that are so easy to understand, install and use, our full line of Pass and Seymour Plug Load Controllable solutions will take a load off your mind and a load off your customers electric bills.

Features & Benefits

Receptacle compliant with 2014 NEC, CA Title 24, and ASHRAE 90.1.

Power button on face serves as a manual override to scheduled programs.

Corrosion-resistant, plated steel strap locked into face and back body to resist pulling away from face/body assembly.

Clear LCD display shows program status, ON/OFF status, current time, and day of the week.

Center panel flips open for easy, three button programming.

.032 inch thick, brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Products meets requirements of UL498B: Receptacles with integral switching means.

Two individual programs can be set to automatically control plug loads.

Bottom half of device features a single receptacle that is automatically controlled by the time clock.

Feed-thru capability allows for downstream control of multiple receptacles.

Permanently molded power symbol on face identifies controlled receptacle in accordance with ASHRAE 90.1, NEC, and Title 24.

Auto-ground eliminates the necessity to terminate grounding conductor in device.

Wire Size: #14 - #10 AWG Copper Conductor Only

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007040029	Country Of Origin	China
Number of Receptacles	1	Features	Plugload, Single Piece Plated Steel Mounting Strap, Timer

Outlet Type	Energy Saving On/Off, Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	RoHS, CSA Listed, CuIUS, UL Listed, FSUL, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.73 in	Product Depth US	1.25 in
Product Height US	2.68 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E472890	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection Location	Back and Side
Phase	Single	Number of Wires	3
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Mounting Type	Box
Wire Connection Type	Screw Terminals	Voltage	125.0 V
Environmental Conditions	UL94 V2		