



Pass and Seymour

Isolated Ground Heavy Duty Spec Grade Single Receptacles, Back and Side Wire, 20A, 125V, Orange

Part No. IG5361

Isolated Ground Heavy-Duty Spec Grade Single Receptacle Back and Side-Wire 20A 125V



Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.

High-impact resistant nylon face resists impacts and scrapes.

Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Side and internal screw-pressure-plate back wire capability with #14 - #10 AWG copper or copper-clad, solid or stranded wire.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Triple-wipe brass contacts ensure lasting, positive contact with plug blades.

Corrosion-resistant plated steel strap.

Plastic barrier isolates grounding terminal from mounting strap and metal boxes.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007653618	Country Of Origin	Mexico
Number of Receptacles	1	Features	Single Piece Plated Steel Mounting Strap

Outlet Type	Isolated Ground, Straight Blade	Application Sector	Commercial
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.38 in	Product Depth US	1.093 in
Product Height US	1.68 in		
Listing Agencies / 3rd Party Agencies			
cUL ListingNumber	E140596	cUL Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Connection Location	Back and Side	Number of Wires	3
Operating Temperature Max	60 °C	Number of Gangs	1
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Mounting Type	Box
Operating Temperature	-40°-60°C	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2