



Isolated Ground Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V

Features & Benefits

IG symbol and Isolated Ground markings for easy identification and circuit delineation.	Face color coding by voltage facilitates locating and mating of proper devices.
High-impact resistant nylon face resists impacts and scrapes.	Corrosion-resistant plated steel strap.
Patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.	Plastic barrier isolates grounding terminal from mounting strap and metal boxes.
Auto-ground clip assures positive ground.	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007045383
Country Of Origin	Mexico	Number of Receptacles	2
Features	Single Piece Plated Steel Mounting Strap	Outlet Type	Isolated Ground, Straight Blade
Application Sector	Commercial	Wall Plate Included	No
Standard	UL498, CSA C22.2 No. 42, FEDSPEC	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.322 in	Product Depth US	0.922 in
------------------	----------	------------------	----------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
---------------------------	--------	---------------------	--------------------------

Connection Location	Back and Side	Number of Wires	3
---------------------	---------------	-----------------	---

Operating Temperature Max	60 °C	Amperage	20 A
---------------------------	-------	----------	------

Number of Poles	Double Pole	Wire Size	14 - 10 AWG
-----------------	-------------	-----------	-------------

Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
----------------	--------	-------------------------	-------

Operating Temperature	-40°-60°C	Wire Connection Type	Internal Pressure Plates, Screw Terminals
-----------------------	-----------	----------------------	--

Voltage	125.0 V
---------	---------
