



3-Way Pilot Lighted Switch, Back and Side-Wire, 15A 120VAC

Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.	Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.
Cam controls fast "make" and positive "break" to minimize arcing.	Heavy-duty bumper pads for quiet operation.
High strength thermoplastic polycarbonate toggle.	Back body made of glass-reinforced nylon.
Locking support provides resistance to face and back body separation.	Oversized silver alloy contacts for long life and better heat dissipation.
Grounding terminal is standard.	Shallow design for ease of installation.
Strap nickel-plated steel with integral ground.	Auto-ground clip assures positive ground.
For covering patents, see www.legrand.us/patents .	For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .

Specifications

General Info

Product Line	Pass & Seymour	Color	Clear
UPC Number	785007195811	Country Of Origin	Mexico
Material	Thermoplastic	Features	Pilot Light
Switch Type	Toggle	Number of Switches	1
Application Sector	Commercial, Industrial	Wall Plate Included	No
Standard	UL 20, FEDSPEC	Warranty Type	1-Year Limited Warranty
Type	Switch		

Dimensions

Product Width US	1.25 in	Product Depth US	1.09 in
------------------	---------	------------------	---------

Product Height US	4.195 in		
-------------------	----------	--	--

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Load Rating	15 A @ 120/277 VAC	Connection Location	Back and Side
-------------	--------------------	---------------------	---------------

Terminal Accommodation	#14 AWG - #10 AWG	Number of Gangs	1
------------------------	-------------------	-----------------	---

Throw Type	Double Throw	Amperage	15 A
------------	--------------	----------	------

Number of Poles	3-Way	Requires Neutral Wire	No
-----------------	-------	-----------------------	----

Indoor/Outdoor	Indoor	Mounting Type	Wall Box
----------------	--------	---------------	----------

Wire Connection Type	Screw Terminals	Voltage	120 VAC, 277 VAC
----------------------	-----------------	---------	------------------

Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		
-----------	--	--	--
