



Pass and Seymour  
Extra Heavy Duty Spec. Grade and Security Switches  
Part No. PS20AC3KL



3-Way Key Lock Back and Side-Wire 20A 120/277V

## Features & Benefits

Back and side wired. Accepts #14 - #10 AWG. Operated by cam lock for maximum security in critical areas. Recommended for tamper-proof installation in schools, public housing, trailer parks, freight yards, etc.

Uses same key as Cat.# 4600 cast enclosure. Key can be removed in both positions.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

## Specifications

### General Info

|                    |                        |                     |                         |
|--------------------|------------------------|---------------------|-------------------------|
| Product Line       | Pass & Seymour         | Finish              | Matte                   |
| UPC Number         | 785007195675           | Country Of Origin   | Mexico                  |
| Material           | Stainless Steel        | Features            | Locking                 |
| Switch Type        | Key                    | Number of Switches  | 1                       |
| Application Sector | Commercial, Industrial | Wall Plate Included | No                      |
| Standard           | UL 20, FEDSPEC         | Warranty Type       | 1-Year Limited Warranty |
| Type               | Switch                 |                     |                         |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.32 in  | Product Depth US | 1.073 in |
| Product Height US | 3.281 in |                  |          |

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

|             |                    |                     |               |
|-------------|--------------------|---------------------|---------------|
| Load Rating | 20 A @ 120/277 VAC | Connection Location | Back and Side |
|-------------|--------------------|---------------------|---------------|

|                        |                   |                 |   |
|------------------------|-------------------|-----------------|---|
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs | 1 |
|------------------------|-------------------|-----------------|---|

|            |              |          |      |
|------------|--------------|----------|------|
| Throw Type | Double Throw | Amperage | 20 A |
|------------|--------------|----------|------|

|                 |       |                       |    |
|-----------------|-------|-----------------------|----|
| Number of Poles | 3-Way | Requires Neutral Wire | No |
|-----------------|-------|-----------------------|----|

|                |        |               |          |
|----------------|--------|---------------|----------|
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
|----------------|--------|---------------|----------|

|                      |                 |         |         |
|----------------------|-----------------|---------|---------|
| Wire Connection Type | Screw Terminals | Voltage | 120.0 V |
|----------------------|-----------------|---------|---------|

|           |                                                                   |
|-----------|-------------------------------------------------------------------|
| Load Type | CFL, Fluorescent, Halogen,<br>Incandescent, LED, Universal, Xenon |
|-----------|-------------------------------------------------------------------|