



Pass and Seymour
30A L2130 Single Receptacle, Orange, Isolated Ground
Part No. IGL2130R

Turnlok Registered Single Receptacle 5-Wire 30A 3-Phase
120/208Volt Isolated Ground



Features & Benefits

UL1449 (latest revision). (1.2 x 50: s 6000V, 8 x 20: s 3000A).

140 joules of energy absorption in each of the three modes.

9,000 amps current handling capability in each of three modes: line to neutral, line to ground, neutral to ground.

1 filtering capacitor for 7 to 1 average noise reduction.

Nominal let-through (suppressed) voltage in all 3 modes, 500V.

LED indicator light.

Response time less than 1 nanosecond for unmounted MOV.

Overcurrent protection in all 3 modes.

Electronic components potted for electrical, mechanical and thermal stability. Thermal protection in all 3 modes.

Leakage current: 0.5 mA at 25: C/120VAC.

3 18mm super MOVs to suppress transients in all modes : equally.

Common mode noise attenuation: 500 KHz to 30 MHz: up to 35 dB (50 ohm source impedance)

Varistor voltage: 150V RMS.

Back and side wire capability including ground terminal.

Operating temperature: -40: C to 85: C (-40: F to 185: F)

Conforms to the latest revision ANSI/IEEE C62.41 (formerly IEEE 587), ANSI/IEEE C62.45.

Specifications

General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007213065	Country Of Origin	Mexico
Number of Receptacles	1	Features	Indicator Lights

Outlet Type	Locking	Application Sector	Commercial, Industrial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.61 in	Product Depth US	1.28 in
Product Height US	2.42 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection Location	Back and Side	Phase	Three
Number of Wires	5	Amperage	30 A
Number of Poles	4-Way	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	L21-30R
Wire Connection Type	Screw Terminals	Voltage	120/208 V