



Pass and Seymour  
30A NEMA L530 Connector - Black Back, White Front Body  
Part No. L530C

Turnlok Registered Connector 3-Wire 30A 125A



## Features & Benefits

|                                                                                             |                                                                                                                                                      |
|---------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.           | Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.                                |
| Raised ribs provide non-slip gripping profile for turning to lock and unlock.               | Double dovetail design provides superior protection against cord pull-out forces.                                                                    |
| Impact- and corrosion-resistant durable nylon 6 shell material.                             | Rounded back contour reduces snags and hang-ups on the job site.                                                                                     |
| Scallop shell design provides non-slip gripping surface for insertion and withdrawal.       | Visible stamped NEMA configuration and device rating.                                                                                                |
| New-design external cord grips provide visible assurance of safe and proper cord retention. | Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber. |

## Specifications

### General Info

|              |                     |                    |            |
|--------------|---------------------|--------------------|------------|
| Product Line | Pass & Seymour      | Color              | Black      |
| UPC Number   | 785007253016        | Country Of Origin  | Mexico     |
| Features     | Corrosion Resistant | Application Sector | Industrial |
| Standard     | UL 498, FEDSPEC     | Warranty Type      | 1-Year     |
| Type         | Connector           |                    |            |

### Dimensions

|                  |        |                   |         |
|------------------|--------|-------------------|---------|
| Product Width US | 2.2 in | Product Length US | 3.33 in |
|------------------|--------|-------------------|---------|

Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 146159 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                 |         |         |    |
|-----------------|---------|---------|----|
| Connector Style | Locking | Flanged | No |
|-----------------|---------|---------|----|

|                        |        |                 |   |
|------------------------|--------|-----------------|---|
| Terminal Accommodation | #4 AWG | Number of Wires | 3 |
|------------------------|--------|-----------------|---|

|          |      |                 |             |
|----------|------|-----------------|-------------|
| Amperage | 30 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

|                |        |                         |        |
|----------------|--------|-------------------------|--------|
| Indoor/Outdoor | Indoor | NEMA Configuration Code | L5-30R |
|----------------|--------|-------------------------|--------|

|         |         |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|