



Pass and Seymour
Industrial Extra Heavy Duty Specification Grade Switch, Brown
Part No. PS15AC3

3-Way Toggle Switch, Back and Side-Wire, 15A 120/277V



Features & Benefits

One-piece toggle molded from chemical-, impact-, and heat-resistant thermoplastic.

Glass-reinforced, chemical-resistant thermoplastic back body for durability, strength, and resistance to harsh cleaners.

Auto-ground clip assures positive ground.

Heavy-duty bumpers for quiet, smooth operation.

Oversized silver-alloy contacts for long life and better heat dissipation.

Heavy-duty, brass alloy, one-piece contact arm virtually eliminates contact bounce.

Shallow design for easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Impact- and chemical-resistant cover.

One-piece nickel-plated brass strap for superior corrosion-resistance.

Cam control and spring actuator for positive "makes and breaks."

Locking support provides resistance to face and back body separation.

Side and external screw-pressure-plate back wire with #14 - #10 AWG copper or copper-clad wire.

Grounding terminal is standard with screw-pressure plate back wire.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007196542
Country Of Origin	Mexico	Material	Thermoplastic

Features		Chemical Resistant	Switch Type	Toggle
Number of Switches	1		Application Sector	Commercial, Industrial
Wall Plate Included	No		Standard	UL 20, FEDSPEC
Warranty Type	1-Year Limited Warranty		Type	Switch
Dimensions				
Product Width US	1.32 in		Product Depth US	1.073 in
Product Height US	3.281 in			
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	140597		cULus Listed	Yes
Technical Information				
Load Rating	15 A @ 120/277 VAC		Connection Location	Back and Side
Terminal Accommodation	#14 AWG - #10 AWG		Number of Gangs	1
Throw Type	Double Throw		Amperage	15 A
Number of Poles	3-Way		Requires Neutral Wire	No
Indoor/Outdoor	Indoor		Mounting Type	Wall Box
Wire Connection Type	Screw Terminals		Voltage	120 VAC, 277 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon			