

2-Pole Toggle Switch, Back and Side-Wire, 30A 120/277V



## Features & Benefits

External screw-pressure-plate back and side wired. Accepts #14 - #10 AWG copper or copper-clad conductors.

Heavy-gauge one-piece copper alloy contact arm virtually eliminates contact bounce.

Cam controls fast "make" and positive "break" to minimize arcing.

Heavy-duty bumper pads for quiet operation.

High strength thermoplastic polycarbonate toggle.

Back body made of glass-reinforced nylon.

Locking support provides resistance to face and back body separation.

Oversized silver alloy contacts for long life and better heat dissipation.

Grounding terminal is standard.

Shallow design for ease of installation.

Strap nickel-plated steel with integral ground.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

|                   |                    |             |               |
|-------------------|--------------------|-------------|---------------|
| Product Line      | Pass & Seymour     | Color       | White         |
| Finish            | Matte              | UPC Number  | 785007195569  |
| Country Of Origin | Mexico             | Material    | Thermoplastic |
| Features          | Chemical Resistant | Switch Type | Toggle        |

|                                       |                                |                        |                                                                |
|---------------------------------------|--------------------------------|------------------------|----------------------------------------------------------------|
| Number of Switches                    | 1                              | Application Sector     | Commercial, Industrial                                         |
| Wall Plate Included                   | No                             | Standard               | UL 498/20, FEDSPEC                                             |
| Warranty Type                         | 1-Year Limited Warranty        | Type                   | Switch                                                         |
| Dimensions                            |                                |                        |                                                                |
| Product Width US                      | 1.32 in                        | Product Depth US       | 1.073 in                                                       |
| Product Height US                     | 3.281 in                       |                        |                                                                |
| Listing Agencies / 3rd Party Agencies |                                |                        |                                                                |
| cULus ListingNumber                   | 140597                         | cULus Listed           | Yes                                                            |
| Technical Information                 |                                |                        |                                                                |
| Load Rating                           | 30 A @ 120/277 VAC             | Connection Location    | Back and Side                                                  |
| Horsepower Rating                     | 2 HP @ 120 VAC, 2 HP @ 240 VAC | Terminal Accommodation | #14 AWG - #10 AWG                                              |
| Number of Gangs                       | 1                              | Throw Type             | Double Throw                                                   |
| Amperage                              | 30 A                           | Number of Poles        | Double Pole                                                    |
| Requires Neutral Wire                 | No                             | Indoor/Outdoor         | Indoor                                                         |
| Mounting Type                         | Wall Box                       | Wire Connection Type   | Screw Terminals                                                |
| Voltage                               | 120/277 V                      | Load Type              | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |