



Pass and Seymour

20A 125V Construction Spec-Grade Tamper-Resistant Single Receptacle, Back and Side Wire, Light Almond

Part No. TR5351LA

Tamper-Resistant Construction Spec Grade Single Receptacles, Back and Side Wire, 20A, 125V



Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

.032 inch thick brass triple-wipe power contacts for lasting retention.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

AC receptacles available in 15 and 20A, 125V.

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

Easily accessed break-off line-contact connecting tab for fast and easy split-circuitwiring.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007241952	Country Of Origin	Mexico
Number of Receptacles	1	Features	Heavy Duty Steel Mounting Strap
Outlet Type	Tamper-Resistant	Application Sector	Commercial
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42
Warranty Type	1-Year Limited Warranty		

Dimensions

Product Width US	1.38 in	Product Depth US	1.19 in
Product Height US	3.28 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2