



Pass and Seymour
20A 125V Extra Heavy Duty Tamper-Resistant Surge Protective Duplex Receptacle, Blue
Part No. TR5362BLSP



Tamper-Resistant Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (with Audible Alarm and LED Indicator), Back and Side Wire, 20A, 125V. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Dual mechanical shutter system to help prevent insertions of foreign objects.

AC receptacles available in 15 and 20 Amp, 125V

.032 inch thick brass triple-wipe power contacts for lasting retention.

Corrosion-resistant plated steel strap is locked in to the face and back body to resist pulling away from the face/body assembly.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
UPC Number	785007020328	Country Of Origin	China
Number of Receptacles	2	Features	Audible Alarm, Indicator Lights
Outlet Type	Straight Blade, Surge Protected, Tamper-Resistant	Application Sector	Commercial
Wall Plate Included	No	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.7 in	Product Depth US	1.4 in
Product Height US	2.75 in		

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Operating Temperature Min	-40 °C	Is Tamper-Resistant	Yes
Connection Location	Back and Side	Phase	Single
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Operating Temperature	-40°-60°C
Wire Connection Type	Internal Pressure Plates, Screw Terminals	Voltage	125.0 V
Environmental Conditions	UL94 V2		