



Pass and Seymour
3.1A Spec Grade USB Outlet, Type A, 20A, Tamper-Resistant, Ivory
Part No. TR5362USBI



Designed for commercial markets with strength and durability in mind, this combination USB charger duplex receptacle features 3.1A overall USB charging capability and is compatible with USB 2.0 & 3.0 devices. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Overall 3.1A USB charging capability: Combination AC duplex receptacles include two 5-volt DC USB ports that work with USB 2.0 & 3.0 compatible devices.	One-piece heat-treated triple-wipe brass power contacts.
AC receptacles are tamper-resistant as standard: patented shutter system prevents improper insertion of foreign objects.	Multiple color options available.
Back and side wire terminals accommodate #14 AWG - #10 AWG stranded and solid copper wire.	Stainless steel auto-ground clips assure positive ground.
Wire Size: #14 - #10 AWG Copper Conductor Only	

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
Finish	Matte	UPC Number	785007031584
Country Of Origin	Vietnam	Number of Receptacles	2
Features	USB-A Charging	Outlet Type	Straight Blade, Tamper-Resistant, USB-Charging
Application Sector	Commercial	Wall Plate Included	No
Standard	CSA Listed, cULus, FSUL, UL Listed, RoHS, FEDSPEC	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.693 in	Product Depth US	1.392 in
Product Height US	2.677 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Additional Information

Product Environmental Profile	Yes
-------------------------------	-----

Technical Information

Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Is Tamper-Resistant	Yes	Connection Location	Back and Side
USB Wattage	15 W	USB Amperage	3.1 A
Number of USBs	2	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Operating Temperature	-40°-60°C	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V		