



Pass and Seymour
15A 125V Heavy Duty Hospital-Grade Duplex Receptacle, Back and Side Wire, Gray
Part No. PS8200HGRY



Heavy-Duty Hospital Grade Duplex Receptacle Back and Side Wire 15A 125V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Two drive screws anchor strap to back body and face.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007860108	Country Of Origin	Mexico
Number of Receptacles	2	Features	Brass Mounting Strap
Outlet Type	Hospital Grade	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42, FEDSPEC

Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection Location	Back and Side
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-15R
Wire Connection Type	Screw Terminals	Voltage	125.0 V
Environmental Conditions	Flammability: UL94 V2		