



PlugTail Registered Decorator Spec Grade Receptacles, 20A, 125V
PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.

Features & Benefits

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

No exposed terminals create a finger safe application before, during, and after installation.

Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections.

Crimped and welded contacts.

Ultrasonically welded polycarbonate connector housing secures terminations and conductors in a UL Listed, finger safe housing.

Pre-stripped connector leads fasten to conductors, easier than standard pigtails.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

PlugTail™ Connector: #12 AWG, THHN, copper conductor, 6" leads, stripped, solid or stranded, for use with PlugTail Receptacles only

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007307986
Country Of Origin	Mexico	Number of Receptacles	2
Features	Decorator Style	Outlet Type	Straight Blade
Application Sector	Commercial	Wall Plate Included	No

Standard	cULus UL498, FEDSPEC	Warranty Type	1-Year Limited Warranty
Dimensions			
Product Width US	1.5 in	Product Depth US	0.625 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Connection Location	Back Only	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	12 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Operating Temperature	-40°-60°C	Wire Connection Type	PlugTail
Voltage	125.0 V		