



Pass and Seymour

Weather-Resistant Heavy Duty Spec Grade Receptacles, Back and Side Wire, 20A, 125V, Gray

Part No. WR5362GRY



Weather-Resistant Heavy-Duty Spec Grade Duplex Receptacle Back and Side-Wire 20A 125V

Features & Benefits

Auto-ground clip assures positive ground.

Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.

Tri-drive brass terminal screws.

Two back wire holes for more wiring flexibility.

UV-resistant nylon face for longer life under adverse environmental conditions.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

WR marking on face as required by UL Standard.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Internal screw-pressure-plate back and side wire capability.

Heavy-duty, brass strap for added strength and ground conductivity.

Two drive screws anchor strap to back body and face where abrupt removal torque is strongest.

.032 inch thick brass triple-wipe power contacts for lasting retention.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Gray
UPC Number	785007242539	Country Of Origin	Mexico

Number of Receptacles	2	Features	Brass Mounting Strap, Weatherproof
Outlet Type	Straight Blade, Weather-Resistant	Application Sector	Commercial
Wall Plate Included	No	Standard	UL 498, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Connection Location	Back and Side
Phase	Three	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Outdoor	NEMA Configuration Code	5-20R
Operating Temperature	-40°-60°C	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V		