



Pass and Seymour  
**Discontinued - Non-Grounding Combination Switches - Sub 693WG, RCD33W**  
Part No. 693W



Double 3-way Combination Switch, 15A, 120/277V

## Features & Benefits

Easily accessible break-off separate or common feed.

Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.

Side wire #12 and #14 AWG.

Two devices fit into the space of one.

Grounding combination devices meet NEC Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                   |                |                         |                         |
|-------------------|----------------|-------------------------|-------------------------|
| Product Line      | Pass & Seymour | Replaced by Part Number | 693WG                   |
| Color             | White          | UPC Number              | 785007693027            |
| Country Of Origin | Mexico         | Application Sector      | Commercial, Residential |
| Standard          | UL20           | Type                    | Combination             |

### Listing Agencies / 3rd Party Agencies

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

### Technical Information

|                          |                       |                  |                          |
|--------------------------|-----------------------|------------------|--------------------------|
| Contact Configuration    | N-O                   | Operating Cycles | 30000                    |
| Actuator                 | Toggle                | Connection       | Side wire, non-grounding |
| Contact Rating           | 15Amp, 120/277Vac     | Amperage         | 15 A                     |
| Number of Poles          | 3-Way                 | Location Rating  | Dry                      |
| Environmental Conditions | Flammability: UL94 V2 |                  |                          |