



radiant Collection  
Discontinued - radiant® 15A Self-Grounding 3-Way Switch, Ivory  
Part No. TM873SI



Enabling control of a single light or fixture from two separate locations, this switch is also designed to automatically ground to the electrical box when installed. Ideal for homes in highly-populated cities or regions where structures may not already be grounded for electrical safety. Part of the radiant Registered Collection, it also features clean lines and smooth paddle action for a sophisticated touch. Made exclusively for use with screwless Wall Plates from the radiant Registered Collection, sold separately. Not sure if your home's electrical wiring is grounded? Your outlets might be a clue. If your home has outlets with only two slots for plug prongs, it is unlikely grounded. Tester devices are also available to confirm proper grounding, or you can always call your local electrician for an inspection.

## Features & Benefits

For use with incandescent lights/bulbs only.

Replaces any standard switch with ease, in as little as 10 minutes.

Uses a paddle switch for smoother control with a low-profile aesthetic.

Features durable, high-impact resistant thermoplastic construction.

Designed to install easily with a narrower back body and captivated mounting screws.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Ensures grounding for electrical safety with automatic ground clip.

## Specifications

### General Info

|                     |                         |                    |                         |
|---------------------|-------------------------|--------------------|-------------------------|
| Product Line        | Pass & Seymour          | Color              | Ivory                   |
| Finish              | Satin                   | UPC Number         | 785007256321            |
| Country Of Origin   | Mexico                  | Material           | Polycarbonate           |
| Features            | Self-Grounding          | Switch Type        | Paddle                  |
| Number of Switches  | 1                       | Application Sector | Commercial, Residential |
| Wall Plate Included | No                      | Standard           | UL 20                   |
| Warranty Type       | 1-Year Limited Warranty | Type               | Switch                  |

Listing Agencies / 3rd Party Agencies

|                     |         |              |     |
|---------------------|---------|--------------|-----|
| cULus ListingNumber | E140597 | cULus Listed | Yes |
|---------------------|---------|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                        |                    |                       |                                                                |
|------------------------|--------------------|-----------------------|----------------------------------------------------------------|
| Load Rating            | 15 A @ 120/125 VAC | Connection Location   | Back and Side                                                  |
| Terminal Accommodation | #14 AWG - #10 AWG  | Number of Gangs       | 1                                                              |
| Throw Type             | Single Throw       | Amperage              | 15 A                                                           |
| Number of Poles        | 3-Way              | Requires Neutral Wire | No                                                             |
| Indoor/Outdoor         | Indoor             | Mounting Type         | Box                                                            |
| Location Rating        | Dry                | Wire Connection Type  | Push Wire, Wire Terminal                                       |
| Voltage                | 120/125 V          | Load Type             | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon |