



Tamper-Resistant Heavy-Duty Decorator Hospital Grade Receptacles, Back and Side Wire, 20A, 125V

Features & Benefits

Dual mechanical shutter system to help prevent insertion of foreign objects.	Auto-ground clip assures positive ground.
Easily accessed break-off line-contact connecting tab for fast and easy split-circuit wiring.	Backed-out tri-drive brass terminal screws for faster installation.
Internal screw-pressure-plate back and side wire capability.	Two back wire holes for additional wiring flexibility.
.032 inch thick brass triple-wipe power contacts.	Two drive screws anchor steel strap to back body and face where abrupt removal torque is greatest.
For covering patents, see www.legrand.us/patents .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Red
Finish	Matte	UPC Number	785007277470
Country Of Origin	Mexico	Number of Receptacles	2
Features	Decorator Style, Single Piece Plated Steel Mounting Strap	Outlet Type	Hospital Grade, Tamper-Resistant
Application Sector	Commercial, Healthcare	Wall Plate Included	No
Standard	UL 498, Fedspec	Warranty Type	1-Year Limited Warranty

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
Product Height US	2.635 in		

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E140596	cULus Listed	Yes
---------------------	---------	--------------	-----

Technical Information

Operating Temperature Min	-40 °C	Is Tamper-Resistant	Yes
Connection Location	Back and Side	Number of Wires	3
Operating Temperature Max	60 °C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Operating Temperature	-40°-60°C	Wire Connection Type	Screw Terminals
Voltage	125.0 V		