



Wattstopper
Power Pack, 120-277V, 50/60Hz, 24VDC, 225mA,
Part No. BZ-200



The BZ-200 power pack switches connected loads On and Off in response to Wattstopper low voltage occupancy sensors. It also provides up to 225mA at 24VDC to power the sensors. This device is constructed with environmentally friendly materials and is RoHS-compliant.

Features & Benefits

Efficient switching power supply provides optimized current output based on number of sensors

Includes short circuit and thermal protection

LED indicates status of relay or presence of low-voltage overcurrent

UL 2043 plenum rated for cost-effective installation

UL listed for control of lighting and plug loads

Tested to NEMA 410 criteria for electronic ballast and driver inrush current

1/2" threaded nipple attaches to standard electrical enclosures through 1/2" knockouts

Specifications

General Info

Product Line	Wattstopper	Color	White
UPC Number	754182938032	Country Of Origin	China
Material	Plastic	Product Series	BZ
Installation Location	Ceiling	Application Sector	Commercial
Warranty Type	5-Year	Type	Power Pack

Dimensions

Product Width US	3.0 in	Product Weight US	0.4 lb
Product Volume US	42.0 cu in	Product Depth US	1.4 in

Product Height US	3.0 in
-------------------	--------

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Operating Temperature Min	-4 °F	Output Voltage	24 VDC
Wire Gauge	18-22 AWG	Operating Temperature Max	131 °F
Input Voltage	120 to 277 VAC	Line Frequency	50 Hz, 60 Hz
Indoor/Outdoor	Indoor	Mounting Type	1/2 in Knockout
Operating Temperature	-4°-131°F	Operating Humidity	5-95% RH (Non-Condensing)
Wire Connection Type	Wire Leads	Connection Type	Wired
Storage Temperature	-40° - 176° F		