



Pass and Seymour

Tamper-Resistant Hospital Grade Receptacles, Smooth Face, Back and Side Wire, 15A, 125V, Ivory

Part No. TR62HI



Tamper-Resistant Hospital Grade Receptacles, Smooth Face, Back and Side-Wire, 15A, 125A

Features & Benefits

Thermoplastic dual mechanism shutter system to help prevent insertion of foreign objects.

Smooth face.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Extra heavy-duty brass, one-piece mounting strap with integral ground.

One-piece, nickel-plated brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Impact-resistant nylon face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Two drive screws anchor strap to back body and face.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Ivory
--------------	----------------	-------	-------

UPC Number	785007145120	Country Of Origin	Mexico
Number of Receptacles	2	Features	Brass Mounting Strap
Outlet Type	Hospital Grade, Tamper-Resistant	Application Sector	Commercial, Healthcare
Wall Plate Included	No	Standard	UL498, CSA C22.2 No. 42, FEDSPEC
Warranty Type	1-Year Limited Warranty		
Dimensions			
Product Width US	1.625 in	Product Depth US	0.9 in
Product Height US	2.75 in		
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	140596	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum
Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Operating Temperature Max	60 °C
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-15R	Operating Temperature	-40°-60°C
Voltage	125.0 V	Environmental Conditions	Flammability: UL94 V2